

Breath Alert® PEAK FLOW METER



Key Benefits

- Designed to measure asthma symptoms to enable early treatment of Asthma and COPD
- Complies with all major international standards for accuracy, reliability and repeatability
- Adult Range 50-800 L/min
- Child Low Range 50-350 L/min
- Re-usable mouthpiece can be easily cleaned and sterilized
- All components made from high grade materials
- · Easy to use
- Individually tested
- Accuracy ± 7.5%
- 1-year warranty

Making Breathing Easier One Step At A Time

Breath Alert®

The Breath Alert® Peak Flow Meter is used to measure peak expiratory flow rate (PEFR) which is the fastest speed a person can blow air out of the lungs taking in as big a breath as possible. It is useful in recognizing early warning signs of asthma attacks.

Measurement of PEFR can be used to:

- determine the severity of asthma or COPD
- check a patient's response to treatment
- warn health care providers of worsening lung function in the absence of discernible symptoms
- identify asthma triggers and diagnose exercise-induced
- provide markers for specific actions in a "Self Managment Plan"

The Breath Alert® Peak Flow Meter is an important part of any asthma management plan.

Ordering Information:

CS0125 - Adult Range Peak Flow Meter - EACH

CS0126 - Low Range Peak Flow Meter - EACH



Unit 1, 20133-102 Avenue, Langley, BC V1M 4B4 Tel: 1.888.310.2186 Fax: 1.888.310.2187 info@carestreammedical.com orders@carestreammedical.com

www.carestreammedical.com