





# Champs protecteurs plats CenterPointLock - Flextend

- ▶ Colerette flottante
- ▶ Code lettré



À découper 

|   |                     | Taille de la colerette | Ouverture du champ (jusqu'à...) | No. de produit | Lettre | Quantité par boîte |
|---|---------------------|------------------------|---------------------------------|----------------|--------|--------------------|
|  | <b>avec adhésif</b> | 1-1/2" (38 mm)         | 1" (25 mm)                      | <b>8727</b>    | H      | 5                  |
|   |                     | 1-3/4" (44 mm)         | 1-1/4" (32 mm)                  | <b>8722</b>    | I      |                    |
|   |                     | 2-1/4" (57 mm)         | 1-3/4" (44 mm)                  | <b>8723</b>    | J      |                    |
|   |                     | 2-3/4" (70 mm)         | 2-1/4" (57 mm)                  | <b>8724</b>    | K      |                    |
|  | <b>sans adhésif</b> | 1-3/4" (44 mm)         | 1-1/4" (32 mm)                  | <b>8752</b>    | I      | 5                  |
|   |                     | 2-1/4" (57 mm)         | 1-3/4" (44 mm)                  | <b>8753</b>    | J      |                    |
|   |                     | 2-3/4" (70 mm)         | 2-1/4" (57 mm)                  | <b>8754</b>    | K      |                    |
| ** sans ouverture de départ   |                     |                        |                                 |                |        |                    |



Précoupés

|   |                     | Taille de la colerette | Ouverture du champ | No. de produit | Lettre | Quantité par boîte |
|---|---------------------|------------------------|--------------------|----------------|--------|--------------------|
|  | <b>avec adhésif</b> | 1-1/2" (38 mm)         | 7/8" (22 mm)       | <b>8743</b>    | H      | 5                  |
|   |                     | 1-1/2" (38 mm)         | 1" (25 mm)         | <b>8744</b>    | H      |                    |
|   |                     | 1-3/4" (44 mm)         | 1-1/8" (29 mm)     | <b>8745</b>    | I      |                    |
|   |                     | 1-3/4" (44 mm)         | 1-1/4" (32 mm)     | <b>8746</b>    | I      |                    |
|   |                     | 2-1/4" (57 mm)         | 1-3/8" (35 mm)     | <b>8747</b>    | J      |                    |
|   |                     | 2-1/4" (57 mm)         | 1-1/2" (38 mm)     | <b>8748</b>    | J      |                    |

### Saviez-vous...

- Ne pas utiliser de tampon gelloderme (7917) ou tout autre protecteur cutané sous un champ protecteur Flextend ou FormaFlex.