




LIMITLESS

POSSIBILITIES.

General Anesthesia Circuits and Masks
Selection, expertise and value to meet anesthesia needs

WHAT YOU NEED. WHEN YOU WANT IT.

What are you looking for in anesthesia gear? Whether you choose to customize or go stock, you'll find the selection, expertise and value to meet your needs every time with Medline. Place your order and count on a strategically located distribution network to deliver innovative solutions on time, every time.




Build The Perfect Circuit.

Our approach to anesthesia gear is quite simple, yet very thoughtful. Use this guide and attached order form to select the best options for each point along the circuit. No extra supplies to sift through, just the components you know you'll use. Whatever your preference, Medline meets the demands of your clinicians and facility.

Anesthesia Turnover Kits.

Reduce SKUs and improve room turnover efficiency with Medline's selection of anesthesia turnover kits. Our custom and stock solutions offer exceptional value while increasing ordering efficiency, freeing up storage space and improving product usage.




YOU MAY WANT TO CONSIDER STOCK.

If you're new to Medline general anesthesia supplies, our stock inventory is a great place to start. Work with your Medline representative to fill your anesthesia gear requirements. Once you try them, and find what works best for you, customize your future orders.

Efficiency

With over 30 distribution centers nationwide, and a fleet of 200+ delivery trucks, circuits and supplies are on time, every time.



UNILIMB CIRCUITS

High Level of Heat and Humidity for Inspired Gases

The inspiratory tube of our unilimb circuits becomes surrounded by the patient's warm exhaled breath. This creates a thermal wrap around the inspiratory tube, which increases the temperature and humidity of inspired gases.

Less Clutter and Disorder In the Anesthesia Field

Remove clutter and disorder from the anesthesia field. Clutter can be further reduced by selecting an optional internal gas sampling line.

Bonded Inspiratory Limb

Prevent disconnects at the patient end, unintentional increases in dead space and mixing of inhaled and exhaled gases with this unique feature.

Adult and Pediatric Circuit

Simplify differentiation with our color-coded design. Inspiratory tubes are green in pediatric circuits and blue in adult circuits.

Wide Variety of Accessory Options

Add your choice of masks, gas sampling lines, filters and HMEs to provide a complete system in a single, cost-efficient package.

Adult Unilimb Circuits

| Item No. | Length | BV Filter or HMEF | Breathing Bag* | Mask | GS Line | Pkg |
|--------------|--------------|-------------------|----------------|--------------|---------|-------|
| DYNJAAF4002 | 40" (102 cm) | 1 | 3 L | | | 20/cs |
| DYNJAAF4300A | 40" (102 cm) | 2 | 3 L | | M/M | 20/cs |
| DYNJAAF6002 | 60" (152 cm) | 1 | 3 L | | | 20/cs |
| DYNJAAF6380 | 60" (152 cm) | 2 | 3 L Slim | | M/M | 20/cs |
| DYNJAAF6390 | 60" (152 cm) | 2 | 3 L Slim | DYNJAAMASK5 | M/M | 20/cs |
| DYNJAAF6500 | 60" (152 cm) | 2 | 2 L Curved | | M/M | 20/cs |
| DYNJAAF6400 | 72" (183 cm) | 2 | 3 L | | M/M | 20/cs |
| DYNJAAF6410 | 72" (183 cm) | 2 | 3 L | DYNJAAMASK5 | M/M | 20/cs |
| DYNJAAF6463 | 72" (183 cm) | HMEF | 3 L Slim | DYNJAAMASKX5 | M/M | 20/cs |

*All breathing bags are not made with natural rubber latex.

Pediatric Unilimb Circuits

| Item No. | Length | BV Filter or HMEF | Breathing Bag* | Mask | GS Line | Pkg |
|--------------|--------------|-------------------|----------------|------|---------|-------|
| DYNJAPF4000A | 40" (102 cm) | 1 | 1 L | | | 20/cs |
| DYNJAPF6002 | 60" (152 cm) | 1 | 1 L | | M/M | 20/cs |
| DYNJAPF6030 | 72" (183 cm) | 2 | 1 L | | M/M | 20/cs |

*All breathing bags are not made with natural rubber latex.



EXPANDABLE DUAL LIMB CIRCUITS

Adult Expandable Dual Limb Circuit

| Item No. | Length | WYE | BV Filter or HMEF | Breathing Bag* | Mask | GS Line | Pkg |
|-------------|---------------|--------------------|-------------------|----------------|--------------|---------|-------|
| DYNJAA0109 | 90" (229 cm) | Parallel | 1 | 3 L | | M/M | 20/cs |
| DYNJAA0110 | 90" (229 cm) | Parallel | 1 | 3 L | DYNJAAMASK5 | M/M | 20/cs |
| DYNJAA0111† | 90" (229 cm) | Parallel | 1 | 3 L | DYNJAAMASK5 | M/M | 20/cs |
| DYNJAA0220 | 90" (229 cm) | Parallel | 1 | 3 L | DYNJAAMASK35 | M/M | 20/cs |
| DYNJAA9010A | 90" (229 cm) | Parallel | 1 | 3 L | DYNJAAMASK6 | M/M | 20/cs |
| DYNJAA9015 | 90" (229 cm) | Parallel | | 3 L | | | 20/cs |
| DYNJAA9020 | 90" (229 cm) | Parallel | | 3 L | DYNJAAMASK6 | M/M | 20/cs |
| DYNJAA9027 | 90" (229 cm) | Parallel | 2 | 3 L | | | 20/cs |
| DYNJAA9120 | 90" (229 cm) | Parallel | 1 | 3 L | | | 20/cs |
| DYNJAA9300† | 90" (229 cm) | Parallel with port | 2 | 3 L | DYNJAAMASK5 | M/M | 20/cs |
| DYNJAA9450 | 90" (229 cm) | Swivel with port | 2 | 3 L | DYNJAAMASK5 | M/M | 20/cs |
| DYNJAA9500 | 90" (229 cm) | Parallel | 2 | 3 L | DYNJAAMASK6 | M/M | 20/cs |
| DYNJAA9980 | 90" (229 cm) | Parallel | HMEF | 3 L | | M/M | 20/cs |
| DYNJAA10150 | 90" (229 cm) | Parallel with port | 1 | 3 L | | M/M | 20/cs |
| DYNJAA10160 | 90" (229 cm) | Parallel with port | 1 | 3 L | DYNJAAMASKX5 | M/M | 20/cs |
| DYNJAA10200 | 90" (229 cm) | Parallel | HMEF | 3 L | DYNJAAMASK35 | M/M | 20/cs |
| DYNJAA10230 | 120" (305 cm) | Parallel | 1 | 3 L | | M/M | 20/cs |
| DYNJAA10232 | 120" (305 cm) | Parallel | 2 | 3 L | | M/M | 20/cs |

*All breathing bags are not made with natural rubber latex.

†Yankauer: Bulb Tip, Suction Tubing: 0.25" x 10 ft

Pediatric Expandable Dual Limb Circuit

| Item No. | Length | WYE | BV Filter or HMEF | Breathing Bag* | Mask | GS Line | Pkg |
|------------|--------------|----------|-------------------|----------------|-------------|---------|-------|
| DYNJAP7207 | 72" (183 cm) | Bi-wye | | 1 L | | | 20/cs |
| DYNJAP7209 | 72" (183 cm) | Bi-wye | | 2 L | | | 20/cs |
| DYNJAP7211 | 72" (183 cm) | Bi-wye | 1 | 1 L | | | 20/cs |
| DYNJAP7213 | 72" (183 cm) | Bi-wye | 1 | 2 L | | | 20/cs |
| DYNJAP7237 | 90" (229 cm) | Bi-wye | 1 | 1 L | | | 20/cs |
| DYNJAP9810 | 90" (229 cm) | Parallel | HMEF | 1 L | | M/M | 20/cs |
| DYNJAP9820 | 90" (229 cm) | Parallel | 1 | 1 L | DYNJAAMASK3 | M/M | 20/cs |
| DYNJAP9830 | 90" (229 cm) | Parallel | 1 | 1 L | | M/M | 20/cs |
| DYNJAP9840 | 90" (229 cm) | Parallel | 2 | 1 L | | M/M | 20/cs |
| DYNJAP9850 | 90" (229 cm) | Parallel | 2 | 2 L | | M/M | 20/cs |

*All breathing bags are not made with natural rubber latex.

Work with your Medline representative to help you choose from the many sizes and configurations to meet your facility's unique needs.

CORRUGATED DUAL LIMB CIRCUITS

Adult Corrugated Dual Limb Circuit

| Item No. | Length | WYE | BV Filter or HMEF | Breathing Bag* | Mask | GS Line | Pkg |
|------------|--------------|----------|-------------------|----------------|-------------|---------|-------|
| DYNJAA0011 | 40" (102 cm) | Parallel | 1 | 3 L | | | 20/cs |
| DYNJAA0103 | 40" (102 cm) | Parallel | 1 | 3 L | | M/M | 20/cs |
| DYNJAA0104 | 40" (102 cm) | Parallel | 1 | 3 L | DYNJAAMASK5 | M/M | 20/cs |
| DYNJAA4071 | 40" (102 cm) | Parallel | 2 | 3 L | | | 20/cs |
| DYNJAA4840 | 40" (102 cm) | Parallel | 2 | 3 L | DYNJAAMASK5 | M/M | 20/cs |
| DYNJAA4005 | 40" (102 cm) | Parallel | | 3 L | | | 20/cs |
| DYNJAA6006 | 60" (152 cm) | Parallel | | 3 L | | | 20/cs |
| DYNJAA6011 | 60" (152 cm) | Parallel | 1 | 3 L | | | 20/cs |
| DYNJAA6021 | 60" (152 cm) | Parallel | 2 | 3 L | | | 20/cs |
| DYNJAA6040 | 60" (152 cm) | Parallel | 1 | 3 L | DYNJAAMASK7 | M/M | 20/cs |


*All breathing bags are not made with natural rubber latex.

Pediatric Corrugated Dual Limb Circuit

| Item No. | Length | WYE | BV Filter or HMEF | Breathing Bag* | Mask | GS Line | Pkg |
|------------|--------------|----------|-------------------|----------------|------|---------|-------|
| DYNJAP0010 | 40" (102 cm) | Parallel | 1 | 1 L | | M/M | 20/cs |
| DYNJAP0012 | 40" (102 cm) | Parallel | 2 | 1 L | | | 20/cs |
| DYNJAP4003 | 40" (102 cm) | Bi-wye | | 1 L | | | 20/cs |
| DYNJAP4007 | 40" (102 cm) | Bi-wye | | 2 L | | | 20/cs |
| DYNJAP4012 | 40" (102 cm) | Parallel | 1 | 1 L | | | 20/cs |
| DYNJAP4015 | 40" (102 cm) | Bi-wye | 1 | 2 L | | | 20/cs |
| DYNJAP4025 | 40" (102 cm) | Parallel | 1 | 2 L | | M/M | 20/cs |
| DYNJAP6109 | 60" (152 cm) | Parallel | 1 | 1 L | | | 20/cs |

*All breathing bags are not made with natural rubber latex.

Choose from a variety of accessory options, including port placement, gas sampling lines, masks and HMEs.




ENGINEERED FOR THE RIGHT GRIP.

After observing and interviewing clinicians in operating rooms across the country, we discovered the secrets to making our anesthesia mask the perfect fit in your hand.

Ergonomic Anesthesia Mask


- » Flexible material—Keeps a tight seal on unique patients without over stressing your grip
- » Finger grips—Relax your hand. No more white knuckles. Use the grips to create a steady, relaxed hold
- » Repositioned connection port—Gives all hand sizes maximum access to patient’s mandible

| Item No. | Description | Size | Pkg |
|--------------|-------------------------------|------|-------|
| DYNJAAMASKX4 | Small Adult Anesthesia Mask | 4 | 50/cs |
| DYNJAAMASKX5 | Regular Adult Anesthesia Mask | 5 | 50/cs |
| DYNJAAMASKX6 | Large Adult Anesthesia Mask | 6 | 50/cs |
| DYNJAAMASKX7 | Wide Adult Anesthesia Mask | 7 | 50/cs |




Flexible Anesthesia Masks

| Item No. | Description | Size | Pkg |
|--------------|-------------------------------|------|-------|
| DYNJAAMASK31 | Neonatal Anesthesia Mask | 1 | 50/cs |
| DYNJAAMASK32 | Infant Anesthesia Mask | 2 | 50/cs |
| DYNJAAMASK33 | Child Anesthesia Mask | 3 | 50/cs |
| DYNJAAMASK34 | Small Adult Anesthesia Mask | 4 | 50/cs |
| DYNJAAMASK35 | Regular Adult Anesthesia Mask | 5 | 50/cs |
| DYNJAAMASK36 | Large Adult Anesthesia Mask | 6 | 50/cs |



Premium Anesthesia Masks

| Item No. | Description | Size | Pkg |
|-------------|-------------------------------|------|-------|
| DYNJAAMASK1 | Neonatal Anesthesia Mask | 1 | 40/cs |
| DYNJAAMASK2 | Infant Anesthesia Mask | 2 | 40/cs |
| DYNJAAMASK3 | Child Anesthesia Mask | 3 | 40/cs |
| DYNJAAMASK4 | Small Adult Anesthesia Mask | 4 | 40/cs |
| DYNJAAMASK5 | Regular Adult Anesthesia Mask | 5 | 20/cs |
| DYNJAAMASK6 | Large Adult Anesthesia Mask | 6 | 20/cs |
| DYNJAAMASK7 | Wide Adult Anesthesia Mask | 7 | 20/cs |



Standard Anesthesia Masks, Pre-Inflated

| Item No. | Description | Size | Pkg |
|--------------|-------------------------------|------|-------|
| DYNJAAMASK9 | Small Premie Anesthesia Mask | 00 | 40/cs |
| DYNJAAMASK10 | Premie Anesthesia Mask | 0 | 40/cs |
| DYNJAAMASK11 | Neonatal Anesthesia Mask | 1 | 40/cs |
| DYNJAAMASK12 | Infant Anesthesia Mask | 2 | 40/cs |
| DYNJAAMASK13 | Child Anesthesia Mask | 3 | 40/cs |
| DYNJAAMASK14 | Small Adult Anesthesia Mask | 4 | 40/cs |
| DYNJAAMASK15 | Regular Adult Anesthesia Mask | 5 | 20/cs |
| DYNJAAMASK16 | Large Adult Anesthesia Mask | 6 | 20/cs |

Scented Anesthesia Masks

| Item No. | Description | Scent | Size | Pkg |
|---------------|--------------------------|------------|------|-------|
| DYNJAAMASK31B | Neonatal Anesthesia Mask | Bubble Gum | 1 | 50/cs |
| DYNJAAMASK31C | Neonatal Anesthesia Mask | Cherry | 1 | 50/cs |
| DYNJAAMASK31S | Neonatal Anesthesia Mask | Strawberry | 1 | 50/cs |
| DYNJAAMASK32B | Infant Anesthesia Mask | Bubble Gum | 2 | 50/cs |
| DYNJAAMASK32C | Infant Anesthesia Mask | Cherry | 2 | 50/cs |
| DYNJAAMASK32S | Infant Anesthesia Mask | Strawberry | 2 | 50/cs |
| DYNJAAMASK33B | Child Anesthesia Mask | Bubble Gum | 3 | 50/cs |
| DYNJAAMASK33C | Child Anesthesia Mask | Cherry | 3 | 50/cs |
| DYNJAAMASK33S | Child Anesthesia Mask | Strawberry | 3 | 50/cs |



HEAT/MOISTURE EXCHANGERS (HME) AND FILTERS

High-Efficiency HMEs

Extensive line of HMEs is available to meet ISO standards and offer a high level of clinical protection to neonatal, pediatric and adult patients.

- » Designed to trap moisture and reduce the risk of moisture build-up in the anesthesia circuit and sampling lines
- » Traps moisture with hygroscopic membrane to provide effective airway humidification
- » Gas sampling ports available with tethered cap

| Item No. | Description | Pkg |
|-------------|------------------------------------|-------|
| DYNJAAHME10 | HME with Port, Straight | 50/cs |
| DYNJAAHME12 | HME No Port, Straight | 50/cs |
| DYNJAAHME14 | HME with Port, Angled | 50/cs |
| DYNJAPHME18 | HME No Port, Angled | 50/cs |
| DYNJAPHME20 | HME with Port, Straight, Pediatric | 50/cs |
| DYNJAPHME23 | HME with Port, Angled, Neonatal | 50/cs |



DYNJAAHME10



DYNJAPHME18

High-Efficiency HMEs and Bacterial Viral (BV) Filters

Medline also provides combination HME and bacterial viral protection* in a complete offering of HMEFs.

- » Products with the BV filter included have an electrostatic hydrophobic membrane that helps protect against cross-contamination
- » BV filters are rated to 0.027 microns at 99.997% or higher efficiency
- » HEPA filtration protection available
- » Pleated hydrophobic mechanical filters available

| Item No. | Description | Pkg |
|---------------|-----------------------------------|-------|
| DYNJAAHME1 | HMEF w/Port, Straight, LG | 50/cs |
| DYNJAAHME5 | HMEF No Port, Straight, LG | 50/cs |
| DYNJAPHME9 | HMEF w/Port, Straight | 50/cs |
| DYNJAAHME11 | HMEF No Port, Straight | 50/cs |
| DYNJAAHME13 | HMEF w/ Port, Angled | 50/cs |
| DYNJAPHME17 | HMEF w/ Port, Straight, Pediatric | 50/cs |
| DYNJAPHME19 | HMEF w/ Port, Angled, Pediatric | 50/cs |
| DYNJAPHME21 | HMEF w/ Port, Angled, Neonatal | 50/cs |
| DYNJAAHMEHEPA | HMEF HEPA, Adult | 50/cs |
| DYNJAAHEPA | Filter, HEPA | 50/cs |
| DYNJAABV1 | Filter, Bacterial Viral | 50/cs |

*A breathing circuit bacterial filter is a device that is intended to remove microbiological and particulate matter from the gases in the breathing circuit



DYNJAAHME9



DYNJAAHME13

ANESTHESIA ACCESSORIES

Breathing Bags*

All Medline breathing bags are 100% ISO 5362 compliant to meet anesthesia needs. Each bag is inspected to ensure the highest levels of quality and delivers uniform inflation to provide a consistent feel.

- » Accommodates all patient needs and physician preferences
- » Offered in a variety of sizes, from 0.5 L to 3 L
- » Available in 2 pleats or a slim 3-pleat style that inflates in a narrow shape to accommodate various hand sizes

| Item No. | Description | Pkg |
|-------------|------------------------------|-------|
| DYNJAA005 | Breathing Bag, 0.5L LF | 20/cs |
| DYNJAA01 | Breathing Bag, 1L LF | 20/cs |
| DYNJAA02 | Breathing Bag, 2L LF | 20/cs |
| DYNJAA03 | Breathing Bag, 3L LF | 20/cs |
| DYNJAACRV02 | Breathing Bag, 2L, Curved LF | 20/cs |

*All breathing bags are not made with natural rubber latex.

Gas Sampling Lines

Each connector meets ISO standards for connections and ensures a secure fit to both anesthesia circuit and machine.

- » Choose from coextruded and standard gas sampling lines
- » Both M/M and M/F connections

| Item No. | Description | Pkg |
|----------|--|-------|
| DYNJAA04 | Gas Sampling Line (0.06 ID), 10 ft., Male/Male | 50/cs |
| DYNJAA05 | Gas Sampling Line (0.06 ID), 10 ft., Male/Male w/ Filter, 0.8 Micron | 50/cs |
| DYNJAA06 | Gas Sampling Line (0.06 ID), 10 ft., Male/Female w/ Filter, 0.8 Micron | 50/cs |
| DYNJAA07 | Gas Sampling Line Filter, 0.8 Micron | 50/cs |
| DYNJAA11 | Gas Sampling Line (0.06 ID), 10 ft., Male/Female | 50/cs |
| DYNJAA15 | Gas Sampling Line (0.047 ID), 10 ft., Male/Male, Coextruded | 50/cs |
| DYNJAA18 | Gas Sampling Line (0.05 ID), 10 ft., Male/Male | 50/cs |
| DYNJAA22 | Gas Sampling Line (0.06 ID), 15 ft., Male/Male | 50/cs |



DYNJAA005, DYNJAA01,
DYNJAA02, DYNJAA03

Anesthesia Accessories

- » Wide variety of connectors with or without gas sampling ports available in bulk or packaged with a circuit
- » Extension sets available to add length to your current anesthesia circuits in both pediatric and adult sizes

| Item No. | Description | Pkg |
|-------------|--|-------|
| DYNJAA10 | Adult Expandable Extension Set, 30"-90" (76-229 cm), 2 tubes | 20/cs |
| DYNJAA20 | Pediatric Expandable Extension Set, 30"-90" (76-229 cm), 2 tubes | 20/cs |
| DYNJAA08 | Straight Connector w/ Gas Sampling Port | 50/cs |
| DYNJAA14 | Flexible Catheter Mount | 50/cs |
| DYNJAATREE1 | Steel Anesthesia Tubing Holder, Tree | 50/cs |
| DYNJAASTRAP | Anesthesia Head Strap | 30/cs |



Custom anesthesia circuit ordering guide

Custom Circuit Options. Most popular highlighted in blue.


Account number/name:

Custom description: (27 characters max)


Monthly usage (each):

Tubing


Expandable



Unlimb



Corrugated




BV Filters




Wye (no wye for a unilimb)


Parallel




Temp Ports




Bifurcated



Temp Ports



Swivel



Connections


Tube to Wye



Tube to Bacterial/Viral Filter




Elbow




Elbow Cap




Additional Options




Mask




Breathing Bag



Gas Sampling Line



Heat Moisture Exchanger





Anesthesia Turnover Kit Components

Yankauer

| | Sterile | Non-Sterile |
|---------------------|-------------------------------------|--------------------------|
| Bulb Tip w/Vent | <input type="checkbox"/> | <input type="checkbox"/> |
| Bulb Tip w/o Vent | <input checked="" type="checkbox"/> | <input type="checkbox"/> |
| Flange Tip w/Vent | <input type="checkbox"/> | <input type="checkbox"/> |
| Flange Tip w/o Vent | <input type="checkbox"/> | <input type="checkbox"/> |

Suction Tubing

| | 1/4" | 3/16" |
|------|-------------------------------------|--------------------------|
| 10ft | <input checked="" type="checkbox"/> | <input type="checkbox"/> |
| 12ft | <input type="checkbox"/> | <input type="checkbox"/> |

Suction Canister

| | Soft | Hard |
|--------|-------------------------------------|--------------------------|
| 1000cc | <input checked="" type="checkbox"/> | <input type="checkbox"/> |
| 1500cc | <input type="checkbox"/> | <input type="checkbox"/> |
| 3000cc | <input type="checkbox"/> | <input type="checkbox"/> |

Pulse Oximeter

Manuf./Item #: _____

Monitor Electrodes

| | Sterile | Non-Sterile |
|-------|--------------------------|-------------------------------------|
| Cloth | <input type="checkbox"/> | <input type="checkbox"/> |
| Foam | <input type="checkbox"/> | <input checked="" type="checkbox"/> |
| Other | <input type="checkbox"/> | <input type="checkbox"/> |

Manuf./Item #: _____

Patient Positioners

Type: _____
Manuf./Item #: _____

Syringes/Needles

Size: _____
Quantity: _____
Manuf./Item #: _____

Temperature Monitoring

Esophageal Stethoscope

| | | | |
|------|-------------------------------------|--------------------------|--------------------------|
| 9FR | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> |
| 12FR | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> |
| 18FR | <input checked="" type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> |
| 24FR | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> |

Multi Use Temp Probe

| | | |
|------|--------------------------|--------------------------|
| 9FR | <input type="checkbox"/> | <input type="checkbox"/> |
| 12FR | <input type="checkbox"/> | <input type="checkbox"/> |

Tympanic Temp Probe

| | |
|----------|--------------------------|
| One Size | <input type="checkbox"/> |
|----------|--------------------------|

Skin Temp Probe

| | |
|----------|--------------------------|
| One Size | <input type="checkbox"/> |
|----------|--------------------------|

Turnover Supplies

| | | | | | | | |
|------------|--------------------------|--------------------------|--------------------------|--------------------------|--------------------------|--------------------------|--------------------------|
| Waste Bags | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> |
| Wipes | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> |
| OR Towel | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> |
| Other | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> |
| Other | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> |
| Other | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> |

Manuf./Item #: _____
Manuf./Item #: _____
Manuf./Item #: _____

Airways

| | Berman | Colored Berman | Guedel |
|--------|-------------------------------------|--------------------------|--------------------------|
| 30 mm | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> |
| 40 mm | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> |
| 50 mm | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> |
| 60 mm | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> |
| 70 mm | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> |
| 80 mm | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> |
| 90 mm | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> |
| 100 mm | <input checked="" type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> |
| 110 mm | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> |
| 120 mm | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> |

Manuf./Item #: _____

Laryngeal Mask Airway

| | Disposable |
|----------|-------------------------------------|
| Size 1 | <input type="checkbox"/> |
| Size 1.5 | <input type="checkbox"/> |
| Size 2 | <input type="checkbox"/> |
| Size 2.5 | <input type="checkbox"/> |
| Size 3 | <input type="checkbox"/> |
| Size 4 | <input checked="" type="checkbox"/> |
| Size 5 | <input type="checkbox"/> |

Manuf./Item #: _____

Endotracheal Tubes

| | | | | | | | | | |
|--------|--------------------------|--------------------------|--------------------------|--------------------------|--------------------------|--------------------------|--------------------------|--------------------------|--------------------------|
| 3 mm | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> |
| 3.5 mm | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> |
| 4 mm | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> |
| 4.5 mm | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> |
| 5 mm | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> |
| 5.5 mm | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> |
| 6 mm | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> |
| 6.5 mm | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> |
| 7 mm | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> |
| 7.5 mm | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> |
| 8 mm | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> |
| 8.5 mm | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> |
| 9 mm | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> |
| 9.5 mm | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> |

Other Items

A COMPREHENSIVE SOURCE FOR ALL YOUR ANESTHESIA PRODUCT NEEDS.

Medline takes pride in being your full-service anesthesia partner. Our broad portfolio includes supplies for general anesthesia, monitored anesthesia care, pain management and regional anesthesia.

If you're ready to learn more, contact our experienced, responsive sales representatives so they can help design a customized product package that meets your specific needs. When you order, you can count on our unsurpassed quality, proven value and quick, efficient delivery.



Medline Industries, Inc. Three Lakes Drive, Northfield, IL 60093

Medline United States
1-800-MEDLINE (633-5463)
medline.com | info@medline.com

Medline Canada
1-800-396-6996
medline.ca | canada@medline.com

Medline México
01-800-831-0898
medlinemexico.com | mexico@medline.com

FOLLOW US 